



## 2 in. EMT Raintight Compression Connector, Uninsulated

By Raco  
Catalog # 2908RT



2 in. EMT Raintight Compression Connector, Uninsulated

### Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Marked with "Wet Location" for easy inspection
- cULus
- Available in trade sizes of 1/2 in. through 4 in.
- Installed knockout seal

### General

Conduit Type	EMT
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel
UPC	050169290897

### Dimensions

Dimensions	2.395 in x 2.607 in x 2.78 in
Height	2.78 in
Length	2.395 in
Trade Size	2 in
Weight	0.563 lb
Width	2.607 in

### Certifications And Compliance

Certified Listed	cULus Listed
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	2080

### Product Assets

[Brochures - HCC Products for Solar](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195970 - 2](#)  
[Product Logo - Conduit](#)  
[Sales Drawings - 2902RT](#)  
[SDS - HCC\\_SDS](#)  
[Sell Sheets - Raintight Steel EMT Compression Fittings](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-2908RT-SPEC-EN | REV 6/2024