



3 in. EMT Raintight Compression Connector, Uninsulated

By Raco
Catalog # [2942RT](#)



3 in. EMT Raintight Compression Connector, Uninsulated

Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Marked with "Wet Location" for easy inspection
- cULus
- Available in trade sizes of 1/2 in. through 4 in.
- Installed knockout seal

General

Conduit Type	EMT
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel
UPC	050169501016

Dimensions

Dimensions	3.946 in x 4.065 in x 4.27 in
Height	4.27 in
Length	3.946 in
Trade Size	3 in
Weight	1.76 lb
Width	4.065 in

Certifications And Compliance

Certified Listed	cULus Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	648

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195970 - 2](#)
[Product Logo - Conduit](#)
[Sales Drawings - 2902RT](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2942RT-SPEC-EN | REV 6/2024