

HUBBELL Power Systems

Station Post Insulator - 15kV / 25kV

By Reuel
Catalog # [U-SPI6012](#)

15kV / 25kV Station Post Insulator - Indoor and Outdoor
Applications - Overall Length = 12.00 in, Top End Outside
Diameter = 4.50 in, Bottom End Outside Diameter = 5.00 in - (4)
1/2 in-13 Threaded Inserts in each End; 3.00 in Dia. B.C.



*Representative Image

General

Application	Station Post Insulator
Bottom Terminal Type	Aluminum Threaded Inserts
Cantilever Bending Strength - Max.	2000
Color	Gray
Number of Bolt Holes - Bottom Terminal	4
Number of Bolt Holes - Top Terminal	4
Number of Sheds	12
Plating - Bottom Terminal	Unplated
Press Minimum	20000
Tensile Strength	10000 lb.
Top Terminal Plating	Unplated
Top Terminal Type	Aluminum Threaded Inserts
Torsional Strength	-
Type	Cast Epoxy Cycloaliphatic

Dimensions

Bottom Terminal Diameter	5 in
Diameter - Bottom Terminal Bolt Circle	3.00 in
Diameter - Bottom Terminal Bolt Holes	1/2-13
Diameter - Large Shed	5.00 in
Diameter - Top Terminal Bolt Circle	3.00 in
Diameter - Top Terminal Bolt Holes	1/2-13
Diameter - Top Terminal Outside	4.50 in
Length	12 in
Weight	12 lb

Electrical Ratings

Minimum Creepage	26.6 in
Minimum Strike	12 in
kV Class	15 kV / 25 kV

Certifications And Compliance

Industry Standard(s)	ANSI C29.9
----------------------	------------

Product Assets

[Literature - Insulators - Reuel](#)
[Sales Drawings - Station Post Insulators](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
REU-USPI6012-SPEC-EN | REV 6/2024