



1/2 in. 90 Degree Liquidtight Connector,
Insulated

By RACO
Catalog # [3542](#)



1/2 in. 90 Degree Liquidtight Connector, Insulated

*Representative Image

Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Insulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

Specifications

Buy American Compliant Certified Listed	Contact Manufacturer • UL Listed • CSA Certified
Environmental Conditions	Wet Location
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 514B
Hazardous Rating(s)	• Class I, Division 2 • Class II Division 1 & 2 • Class III, Division 1 & 2

Dimensions

Package Height	4.000 in
Length	1.17 in
Trade Size	1/2 in
Package Weight	7.373 lb.

Package Length	8.625 in
Package Width	4.938 in
Weight	0.251 lb.
Height	2.146 in
Width	2.36 in
Dimensions	1.17 in x 2.36 in x 2.146 in

General

Conduit Type	Liquidtight
Product Family	Liquidtight
Insulation Type	Insulated
Fitting Type	Connectors
Product Type	Commercial Fittings
UPC	050169035429
Material	Steel/Malleable Iron

Logistics

Minimum Pack Quantity	25
Pallet Quantity	6400
Carton Quantity	100

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)