



Compression Deadend

by FARGO
Catalog ID: SEDA1309SSAC

Compression Deadend, Conventional 2-Die, Single Tongue, for ACSS
336.4 kcmil 26/7, With Terminal



* Representative image

Product Details

General

Aluminum Die	20AH
Bolt Installation Torque (Recommended)	0 ft-lbs
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	2
Number of Pad Holes	0
Press Minimum	12 to
Product Category	Assemblies
Style	Conventional 2-Die, Single Tongue
Tension Range	0 lb
Type	Compression
UPC	096359504290

Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0°
Clamping - Maximum	0 in
Clamping - Minimum	0 in

Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in
Diameter - Outside	0.72 in
Diameter - Pad Bolt	0 in
Length - Pin	0 in
Length Before Compression	16.9 in
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Width - Pad	2 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	ACSS-Linnet-336.4-26/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com