



3/4 in. Color-Coded 90° Strain Relief Cord Connector, Malleable Iron, Yellow

By Raco
Catalog # 3795-5



*Representative Image

3/4 in. Color-Coded 90° Strain Relief Cord Connector, Malleable Iron, Yellow

Features

- Malleable iron construction provides mechanical strength and durability
- Neoprene grommets are color-coded by cable diameter allowing for quick and easy identification
- Metallic components are zinc plated for corrosion protection
- Unique grommet design is forced up and around the cord when the nut is tightened creating a liquidtight seal
- Time saving and easy installation - no need to disassemble the fitting for cord installation
- Additional colors and sizes available

General

| | |
|-------------|---|
| Application | For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations |
| Color | Yellow |
| Material | Malleable Iron |
| UPC | 050169983348 |

Dimensions

| | |
|------------|-----------------------------|
| Dimensions | 3.25 in x 1.44 in x 1.44 in |
| Height | 1.44 in |
| Length | 3.25 in |
| Trade Size | 0.75 in |
| Weight | 0.457 lb |
| Width | 1.44 in |

Conductor Related

| | |
|-------------|--------------|
| Cable Range | .65 - .75 in |
|-------------|--------------|

Certifications And Compliance

| | |
|------------------|--------------|
| Certified Listed | cULus Listed |
| Nema Rating | NEMA 4 |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 10 |
| Minimum Pack Quantity | 10 |
| Pallet Quantity | 2520 |

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Customer Notices - Prop65_Cancer](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Color-Coded Cord Grip Connectors](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-37955-SPEC-EN | REV 6/2024