



Compression Deadend

by FARGO
Catalog ID: SEDA4118SSAC

Compression Deadend, Conventional 2-Die, Single Tongue, for ACSS
954.0 kcmil 45/7, With Terminal



* Representative image

Product Details

General

Aluminum Die	30AH
Bolt Installation Torque (Recommended)	0 ft-lbs
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	4
Number of Pad Holes	0
Press Minimum	60 to
Product Category	Assemblies
Style	Conventional 2-Die, Single Tongue
Tension Range	0 lb
Type	Compression
UPC	096359474944

Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Clamping - Maximum	0 in
Clamping - Minimum	0 in

Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in
Diameter - Outside	1.165 in
Diameter - Pad Bolt	0 in
Length - Pin	0 in
Length Before Compression	21.8 in
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Weight	7.450 lb
Width - Pad	3 in

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Conductor Compatibility	ACSS-Rail-954-45/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com