



# Compression Deadend

by FARGO  
Catalog ID: SEDA6610

Compression Deadend, Conventional 2-Die, Double Tongue, for ACSR  
2312.0 kcmil 76/19, With Terminal



\* Representative image

## Product Details

### General

|                                        |                                   |
|----------------------------------------|-----------------------------------|
| Aluminum Die                           | 44AH                              |
| Bolt Installation Torque (Recommended) | 0 ft-lbs                          |
| Compression Method                     | Conventional (2 die system)       |
| Inhibitor Loaded                       | No                                |
| Material                               | Aluminum; Steel                   |
| Material - Body                        | Seamless Extruded Aluminum Alloy  |
| Material - Eye                         | Galvanized Forged Steel           |
| Material - Hardware                    | Aluminum Alloy                    |
| Material - Terminal                    | Seamless Extruded Aluminum Alloy  |
| Number of Bolt Holes                   | 4                                 |
| Number of Pad Holes                    | 0                                 |
| Press Minimum                          | 100 to                            |
| Product Category                       | Assemblies                        |
| Style                                  | Conventional 2-Die, Single Tongue |
| Tension Range                          | 0 lb                              |
| Type                                   | Compression                       |
| UPC                                    | 096359388036                      |

### Dimensions

|                                    |      |
|------------------------------------|------|
| Actual Clamp Strand Diameter Range | 0 in |
| Adjustment Step                    | 0 in |
| Angle - Pad                        | 0 °  |
| Clamping - Maximum                 | 0 in |
| Clamping - Minimum                 | 0 in |

|                              |          |
|------------------------------|----------|
| Diameter - Clamping Hardware | 0 in     |
| Diameter - Clevis Pin        | 0 in     |
| Diameter - Eye Hole          | 0 in     |
| Diameter - Inside            | 0 in     |
| Diameter - Outside           | 1.802 in |
| Diameter - Pad Bolt          | 0 in     |
| Length - Pin                 | 0 in     |
| Length Before Compression    | 26.4 in  |
| Take Up                      | 0 in     |
| Thickness - Pad              | 0 in     |
| Total Adjustment             | 0 in     |
| Width - Pad                  | 4 in     |

### Electrical Ratings

|                     |               |
|---------------------|---------------|
| Voltage Application | EHV; Standard |
|---------------------|---------------|

### Conductor Related

|                                     |                          |
|-------------------------------------|--------------------------|
| Conductor Compatibility             | ACSR-Thrasher-2312-76/19 |
| Conductor Diameter (Main) - Maximum | 0 in                     |
| Conductor Diameter (Main) - Minimum | 0 in                     |
| Messenger Diameter - Maximum        | 0 in                     |
| Messenger Diameter - Minimum        | 0 in                     |

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
 210 N. Allen Centralia, MO 65240 USA  
 Phone: (573) 682-5521  
 Fax: (573) 682-8475  
 Email: [hpscs@hubbell.com](mailto:hpscs@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
 Fax: +1-573-682-8516  
 Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)