

Catalog # 813C

4 IN. SQUARE EXPOSED WORK COVER

2.625 IN. DIA. 30A-60A RECEPTACLE

Ideal for exposed work environments to support a variety of electrical devices. Our exposed work covers are made from heavy duty, 16-gauge, galvanized steel and come in 22 configurations to fit your needs.

FEATURES

- Exposed work covers include break-off lock nuts or required hardware
- Exposed work covers meet the requirements of the 2020 NEC Article 250.146 (A). No bonding jumper is required for covers with: (1) Crushed corners (2) Two or more device attachment fasteners that are permanent with thread-locking, screws, or nut-locking means (3) Insulating retaining washer removed for at least one device attachment screw
- Cover is packed with printed catalog number, compliances and QR code for installation instructions



APPLICATIONS

Surface covers are used to support switches or receptacles in areas where the box is surface mounted or positioned in exposed work applications.



CERTIFICATIONS



SPECIFICATIONS

UPC NUMBER:	050169999882	I2OF5:	50050169999887
PRODUCT LENGTH/DEPTH (IN.):	0.56	STANDARD CARTON QTY:	10
PRODUCT WIDTH (IN.):	4.12	MIN ORDER QTY:	10
PRODUCT HEIGHT (IN.):	4.12		
WT. PRODUCT. (LBS.):	0.300		
PACKAGE TYPE:	LOOSE		
PRODUCT UPC-A LABELED:	YES		

PACKAGING