



\* Representative image

## T179603S

by Acme Electric  
Catalog ID: T179603S

Prop65\_Cancer&Reproductive

Low Voltage Lighting Transformer - Single Phase, 120 - 12V, 750VA

- Copper lead wires for hardwiring
- Primary and secondary overload protection
- Full fault current carrying Farady Shield
- Single and dual knockouts

## Product Details

### General

|                       |                                  |
|-----------------------|----------------------------------|
| Circuit Breaker Style | Magnetic Toggle On/Off Breaker   |
| Construction          | Encapsulated                     |
| Electrostatic Shield  | Shielded                         |
| Max Temperature Rise  | 115 Degrees Celsius              |
| Mounting Type         | Wall                             |
| Primary Voltage       | 120 V                            |
| Product Category      | Low Voltage Lighting Transformer |
| Secondary Voltage     | 12 V                             |
| UL Insulation Class   | 180°C                            |
| UPC                   | 047503090244                     |
| Winding Material      | CU                               |

### Dimensions

|        |          |
|--------|----------|
| Height | 11.68 in |
| Length | 4.57 in  |
| Weight | 18 lb    |
| Width  | 4.66 in  |

### Electrical Ratings

|                  |       |
|------------------|-------|
| Frequency Rating | 60 Hz |
| Primary Voltage  | 120 V |

### Certifications and Compliance

|              |             |
|--------------|-------------|
| CSA Standard | C22.2 No 47 |
| Nema Rating  | NEMA 2      |
| UL Standard  | UL 506      |