



U-SWI4082ECFF

By Hubbell
Catalog # U-SWI4082ECFF

SWITCH INSUL. ELEC. CONN. 8.25



*Representative Image

Features

- Switch Insulator
- 27kV

Application

Switch Insulator

General

Bottom Terminal Type	Aluminum Threaded Inserts
Cantilever Bending Strength - Routine	1200 lb
Color	Gray
Number of Bolt Holes - Bottom Terminal	5
Number of Bolt Holes - Top Terminal	5
Number of Sheds	7
Plating - Bottom Terminal	Unplated
Press Minimum	20000
Tensile Strength	5000 lb.
Top Terminal Plating	Unplated
Top Terminal Type	Aluminum Threaded Inserts
Type	Cast Epoxy Cycloaliphatic

Dimensions

Bottom Terminal Diameter	4.00 in
Diameter - Bottom Terminal Bolt Circle	2.00 in
Diameter - Bottom Terminal Bolt Holes	3/8-16
Diameter - Large Shed	4.62 in
Diameter - Top Terminal Bolt Circle	2.00 in
Diameter - Top Terminal Bolt Holes	3/8-16
Diameter - Top Terminal Outside	4.00 in
Length	8.25 in
Weight	6.0 lb

Electrical Ratings

Minimum Creepage	23.45 in
Minimum Strike	8.50 in
kV Class	27 kV

Certifications and Compliance

Industry Standard(s)	ANSI C29.9
----------------------	------------



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
REU-U-SWI4082ECFF-SPEC-EN | REV 9/2023