

## Universal Air Bushing - 25kV

By Reuel  
Catalog # [U-UAB125](#)

25kV-600A Universal Air Bushing - Indoor and Outdoor  
Applications Rated per IEEE 386 - Overall Length = 14.59 in,  
Strike Distance = 19.04 in - Aluminum Conductor



\*Representative Image

### Application

Any

### General

Bottom Terminal Type	Aluminum-Threaded
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Air
Material - Flange	If Supplied Stainless Steel or Mild Steel
Material - Insulation	Cast Epoxy Cycloaliphatic
Mounting Position	Any
Number of Bolt Holes - Bottom Terminal	1
Number of Sheds	13
Plating - Bottom Terminal	Unplated
Test Tap	No
Thread Type - Bottom Terminal	Female
Thread Type - Top Terminal	Male
Top Terminal Plating	Unplated
Top Terminal Type	Aluminum-Threaded
Type	Distribution Transformer Bushings

### Dimensions

Above Flange Length	9.98 in
Below Flange Length	4.62 in
Bottom Terminal Min. Thread Length	0.88 in
Diameter - Above Flange Maximum	2.50 in
Diameter - Bottom Terminal Bolt Holes	5/8-11
Flange Outside Diameter Length	3.71 in
Length - Insulation Above Flange	14.59 in
Length - Insulation Below Flange	8.66 in
Length - Insulation Below Flange	4.62 in
Thread Size - Bottom Terminal	5/8-11
Top Terminal Min. Thread Length	1.25 in
Weight	4.25 lb

### Electrical Ratings

Current Overload	900 A
Current Rating	600 A
Minimum Creepage	19.40 in
Minimum Strike	8.66 in
Withstand Current - Short Time (10 cycles)	25000 A
Withstand Current - Short Time (3 sec)	10000 A
kV Class	25 kV

### Product Assets

[Literature - Bushings - Reuel \(SF02020E\)](#)  
[Sales Drawings - 600 Amp Universal Air Bushing \(DSUAB-01\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
REU-U-UAB125-SPEC-EN | REV 1/2024