

Bushing Well - 15kV

By Reuel
Catalog # [U-UBW95](#)

15kV-200A Bushing Well - Indoor Applications Rated per IEEE 386 - Overall Length = 9.25 in, Strike Distance = 12.00 in - Aluminum Conductor



*Representative Image

Application

Any

General

Bottom Terminal Type	Aluminum-Threaded
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Air
Material - Flange	If Supplied Stainless Steel or Mild Steel
Material - Insulation	Cast Epoxy Cycloaliphatic
Mounting Position	Any
Number of Bolt Holes - Bottom Terminal	1
Number of Sheds	16
Plating - Bottom Terminal	Unplated
Test Tap	No
Thread Type - Bottom Terminal	Female
Thread Type - Top Terminal	Male
Top Terminal Plating	Unplated
Top Terminal Type	Aluminum-Threaded
Type	Distribution Transformer Bushings
UPC	096359726173

Dimensions

Above Flange Length	8.13 in
Below Flange Length	1.13 in
Diameter - Above Flange Maximum	2.50 in
Diameter - Bottom Terminal Bolt Holes	3/8-16
Dimensions	3.71 in x 3.71 in x 9.25 in
Flange Outside Diameter	3.71 in
Height	9.25 in
Length	3.71 in
Length - Insulation Above Flange	7.13 in
Length - Insulation Below Flange	1.13 in
Thread Size - Bottom Terminal	3/8-16
Weight	2.52 lb
Width	3.71 in

Electrical Ratings

Current Overload	300 A
Current Rating	200 A
Minimum Creepage	12.00 in
Minimum Strike	7.13 in
Withstand Current - Short Time (10 cycles)	10000 A
Withstand Current - Short Time (3 sec)	3500 A
kV Class	15 kV

Product Assets

[Catalogs - Reuel Apparatus Bushings \(SF_02_020E_Literature - Bushings - Reuel \(SF02020E\)\)](#)
[Sales Drawings - 200-Amp Bushing Well \(DSUBW-01\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
REU-U-UBW95-SPEC-EN | REV 1/2024