

HUBBELL Power Systems

Standoff Insulator - 15kV

By Reuel

Catalog # [U-SOI3760HCFF](#)

15kV Standoff Insulator - High Creep for Indoor and Outdoor Applications - Overall Length = 6.00 in, Shed Outside Diameter = 3.75 in - (4) 3/8 in-16 Threaded Inserts in each End; 2.00 in Dia. B.C. with (1) 1/2 in-13 Threaded Insert



*Representative Image

General

Application	Stand-Off Insulator - High Creep
Bottom Terminal Type	Aluminum Threaded Inserts
Cantilever Bending Strength - Routine	1250 lb
Color	Gray
Number of Bolt Holes - Bottom Terminal	5
Number of Bolt Holes - Top Terminal	5
Number of Sheds	6
Plating - Bottom Terminal	Unplated
Press Minimum	20000
Tensile Strength	3000 lb.
Top Terminal Plating	Unplated
Top Terminal Type	Aluminum Threaded Inserts
Torsional Strength	-
Type	Cast Epoxy Cycloaliphatic

Dimensions

Bottom Terminal Diameter	3.75 in
Diameter - Bottom Terminal Bolt Circle	2.00 in
Diameter - Bottom Terminal Bolt Holes	3/8-16
Diameter - Large Shed	3.75 in
Diameter - Top Terminal Bolt Circle	2.00 in
Diameter - Top Terminal Bolt Holes	3/8-16
Diameter - Top Terminal Outside	3.75 in
Length	6 in
Weight	3.8 lb

Electrical Ratings

Minimum Creepage	12.41 in
Minimum Strike	6 in
kV Class	15 kV

Certifications And Compliance

Industry Standard(s)	ANSI C29.9
----------------------	------------

Product Assets

[Literature - Insulators - Reuel](#)

[Sales Drawings - Stand-Off Insulators \(High Creep\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
REU-USOI3760HCFF-SPEC-EN | REV 6/2024