



\* Representative image

## T3225K0013BK20S

by Acme Electric

Catalog ID: T3225K0013BK20S

Prop65\_Cancer&Reproductive

Non Linear Load Transformer - Three Phase, 480Δ - 208Y/120V, 225kVA, K20

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection

### Product Details

#### General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Electrostatic Shield	Shielded
K Factor	20
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Non Linear Load Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503094518
Winding Material	AL
kVA	225

#### Dimensions

Height	45.6 in
Length	35.5 in
Weight	1938 lb
Width	39.5 in

#### Electrical Ratings

Efficiency	98.94%
Frequency Rating	60 Hz
Primary Voltage	480D V

## Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561