

Bushing Well - 25kV

By Reuel
Catalog # [U-UBW125B](#)

25kV-200A Bushing Well - Indoor Applications Rated per IEEE
386 - Overall Length = 10.74 in, Strike Distance = 16.00 in -
Aluminum Conductor



*Representative Image

Features

- Bushing well
- Copper Conductor

Application

Any

General

Bottom Terminal Type	Aluminum-Threaded
Catalog Number	U-UBW125B
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Air
Material - Flange	If Supplied Stainless Steel or Mild Steel
Material - Insulation	Cast Epoxy Cycloaliphatic
Mounting Position	Any
Number of Bolt Holes - Bottom Terminal	1
Number of Bolt Holes - Top Terminal	0
Number of Sheds	16
Plating - Bottom Terminal	Unplated
Test Tap	No
Thread Type - Bottom Terminal	Female
Thread Type - Top Terminal	Male
Top Terminal Plating	Unplated
Top Terminal Type	Aluminum-Threaded
Type	200 Amp Bushing Well

Dimensions

Above Flange Length	9.63 in
Below Flange Length	1.13 in
Diameter - Above Flange Maximum	2.50 in
Diameter - Bottom Terminal Bolt Holes	3/8-16
Flange Outside Diameter	3.71 in
Length	10.74 in
Length - Insulation Above Flange	8.63 in
Length - Insulation Below Flange	1.13 in
Thread Size - Bottom Terminal	3/8-16
Weight	2.95 lb

Electrical Ratings

Current Overload	300 A
Current Rating	200 A
Minimum Creepage	16 in
Minimum Strike	8.63 in
Withstand Current - Short Time (10 cycles)	10000 A
Withstand Current - Short Time (3 sec)	3500 A
kV Class	25 kV

Product Assets

[Literature - Bushings - Reuel](#)
[Sales Drawings - 200-Amp Bushing Well](#)
[Specifications - U-UBW125B](#)