



# Compression Repair Sleeve

by ANDERSON  
Catalog ID: RS1709

Compression Sleeve, Uni-Grip, Repair Sleeve, for AAC, AAAC, ACAR, ACSR,ACSS, Dia. Range 0.766-0.855



\* Representative image

## Product Details

### General

|                    |                              |
|--------------------|------------------------------|
| Compression Method | Uni-Grip (single die system) |
| Die Size           | 09CD                         |
| Inhibitor Loaded   | No                           |
| Material           | Aluminum Alloy               |
| Press Minimum      | 12 to                        |
| Tension Range      | 0 lb                         |
| UPC                | 096359363880                 |

### Dimensions

|                                    |          |
|------------------------------------|----------|
| Adjustment Step                    | 0 in     |
| Assembly Rating (Ultimate)         | 0 lb     |
| Insulator / Conductor Hole Spacing | 0 in     |
| Length Before Compression          | 10.8 in  |
| Weight                             | 0.882 lb |

### Electrical Ratings

|                     |          |
|---------------------|----------|
| Voltage Application | Standard |
|---------------------|----------|

### Conductor Related

|                                     |                                                                                                                                                                                        |
|-------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor Compatibility             | ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37 |
| Conductor Diameter (Main) - Maximum | 0 in                                                                                                                                                                                   |
| Conductor Diameter (Main) - Minimum | 0 in                                                                                                                                                                                   |
| Conductor Diameter - Maximum        | 0.855 in                                                                                                                                                                               |
| Conductor Diameter - Minimum        | 0.766 in                                                                                                                                                                               |

|                              |               |
|------------------------------|---------------|
| Conductor Diameter Range     | 0.766 - 0.855 |
| Messenger Diameter - Maximum | 0 in          |
| Messenger Diameter - Minimum | 0 in          |

Certifications and Compliance

|           |    |
|-----------|----|
| UL Listed | No |
|-----------|----|

Logistics

|                 |         |
|-----------------|---------|
| Pallet Quantity | 1080 EA |
|-----------------|---------|

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscs@hubbell.com](mailto:hpscs@hubbell.com)

International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)