



# Compression Repair Sleeve

by ANDERSON  
Catalog ID: RS1712

Compression Sleeve, Uni-Grip, Repair Sleeve, for AAC, AAAC, ACAR, ACSR,ACSS, Dia. Range 1.026 -1.131



\* Representative image

## Product Details

### General

|                    |                              |
|--------------------|------------------------------|
| Compression Method | Uni-Grip (single die system) |
| Die Size           | 12CD                         |
| Inhibitor Loaded   | No                           |
| Material           | Aluminum Alloy               |
| Press Minimum      | 60 to                        |
| Tension Range      | 0 lb                         |
| UPC                | 096359363910                 |

### Dimensions

|                                    |          |
|------------------------------------|----------|
| Adjustment Step                    | 0 in     |
| Assembly Rating (Ultimate)         | 0 lb     |
| Insulator / Conductor Hole Spacing | 0 in     |
| Length Before Compression          | 14.4 in  |
| Weight                             | 3.597 lb |

### Electrical Ratings

|                     |               |
|---------------------|---------------|
| Voltage Application | EHV; Standard |
|---------------------|---------------|

### Conductor Related

|                                     |                                                                                                                                                                                                                                                                   |
|-------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor Compatibility             | ACSR-Starling-715.5-26/7;ACSR-Redwing-715.5-30/19;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Tern-795-45/7;ACSR-Condor-795-54/7;ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61;AAC-Magnolia-954-37;AAC-Goldenrod-954-61 |
| Conductor Diameter (Main) - Maximum | 0 in                                                                                                                                                                                                                                                              |
| Conductor Diameter (Main) - Minimum | 0 in                                                                                                                                                                                                                                                              |
| Conductor Diameter - Maximum        | 1.131 in                                                                                                                                                                                                                                                          |

|                              |               |
|------------------------------|---------------|
| Conductor Diameter - Minimum | 1.026 in      |
| Conductor Diameter Range     | 1.026 - 1.131 |
| Messenger Diameter - Maximum | 0 in          |
| Messenger Diameter - Minimum | 0 in          |

Certifications and Compliance

|           |    |
|-----------|----|
| UL Listed | No |
|-----------|----|

Logistics

|                 |        |
|-----------------|--------|
| Pallet Quantity | 300 EA |
|-----------------|--------|

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscs@hubbell.com](mailto:hpscs@hubbell.com)

International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)