



TB100A008C

by Acme Electric
Catalog ID: TB100A008C

Industrial Control Transformer .100 kVA, 240 X 480 Primary Volts - 120 Secondary Volts

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are sealed within an epoxy encapsulant encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

- Secondary fuse clips factory installed, where applicable
- Twenty year limited warranty
- UL Listed and CSA Certified or cUL
- Epoxy encapsulated design protects core & coil assembly from potentially damaging contaminants

Product Details

General

Construction	Encapsulated
Secondary Voltage	110/115/120 V
UPC	047503002971

Dimensions

Height	4 in
Length	3.46 in
Weight	4.4 lb
Width	3.38 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	220, 230, 240 X 440, 460, 480 V
Voltage Rating	100 V

Certifications and Compliance

CSA Standard	CSA 22.2 NO 66.1;CSA 22.2 NO 66.2
Industry Standard(s)	cUL
UL Standard	UL 5085-1;UL 5085-2

