

# Compression Deadend

by FARGO  
Catalog ID: SEDA1808SSACNT

Compression Deadend, Conventional 2-Die, Single Tongue, for ACSS  
477.0 kcmil 24/7, Without Terminal



\* Representative image

## Product Details

### General

Aluminum Die	24AH
Bolt Installation Torque (Recommended)	0 ft-lbs
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Number of Bolt Holes	2
Number of Pad Holes	0
Press Minimum	60 to
Product Category	Assemblies
Style	Conventional 2-Die, Single Tongue
Tension Range	0 lb
Terminal Option	No
Type	Compression
UPC	096359380191

### Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0°
Clamping - Maximum	0 in
Clamping - Minimum	0 in

Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in
Diameter - Outside	0.846 in
Diameter - Pad Bolt	0 in
Length - Pin	0 in
Length Before Compression	18.6 in
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Weight	4.400 lb
Width - Pad	2.5 in

### Electrical Ratings

Voltage Application	Standard
---------------------	----------

### Conductor Related

Conductor Compatibility	ACSS-Flicker-477-24/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)