



Compression Deadend

by FARGO
Catalog ID: SEDA2209

Compression Deadend, Conventional 2-Die, Single Tongue, for ACSR
556.5 kcmil 26/7, With Terminal



* Representative image

Product Details

General

Aluminum Die	24AH
Bolt Installation Torque (Recommended)	0 ft-lbs
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	4
Number of Pad Holes	0
Press Minimum	60 to
Product Category	Assemblies
Style	Conventional 2-Die, Single Tongue
Tension Range	0 lb
Type	Compression
UPC	096359511892

Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Clamping - Maximum	0 in
Clamping - Minimum	0 in

Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in
Diameter - Outside	0.927 in
Diameter - Pad Bolt	0 in
Length - Pin	0 in
Length Before Compression	15.8 in
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Weight	6.360 lb
Width - Pad	3 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	ACSR-Dove-556.5-26/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

For further technical assistance, please contact us

Domestic Customer Service
 Hubbell Power Systems
 210 N. Allen Centralia, MO 65240 USA
 Phone: (573) 682-5521
 Fax: (573) 682-8475
 Email: hpscs@hubbell.com

International Customer Service
 Phone: +1-573-682-5521
 Fax: +1-573-682-8516
 Email: hpsintlcs@hubbell.com