

# TB2000N005F4

by Acme Electric

Catalog ID: TB2000N005F4



ICT 2KVA 208,230,460 -115 F4

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

## Product Details

---

### General

Application	Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.
Color	Black
Secondary Voltage	115 V
UPC	047503009994

## Dimensions

Dimensions	7.98 in x 7 in x 6.9 in
Height	6.9 in
Length	7.98 in
Weight	30 lb
Width	7 in

## Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	208/230/460 V

## Logistics

Carton Quantity	1
Pallet Quantity	24