

TB1000N008F1

by Acme Electric

Catalog ID: TB1000N008F1



ICT 1KVA 240X480-120 F1

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

Product Details

General

| | |
|--------------------|---|
| <p>Application</p> | <p>Acme's CE Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.</p> |
|--------------------|---|

| | |
|-------------------|--------------|
| Color | Black |
| Secondary Voltage | 120 V |
| UPC | 047503010952 |

Dimensions

| | |
|------------|----------------------------|
| Dimensions | 6.606 in x 7 in x 6.901 in |
| Height | 6.901 in |
| Length | 6.606 in |
| Weight | 29.8 lb |
| Width | 7 in |

Electrical Ratings

| | |
|------------------|-------------|
| Frequency Rating | 50/60 Hz |
| Primary Voltage | 240 X 480 V |

Logistics

| | |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|