

TB100N006F2

by Acme Electric

Catalog ID: TB100N006F2



ICT .100KVA 208,277 - 120 F2

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

Product Details

General

| | |
|--------------------|---|
| <p>Application</p> | <p>Acme's CE Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.</p> |
|--------------------|---|

| | |
|-------------------|--------------|
| Color | Black |
| Secondary Voltage | 120 V |
| UPC | 047503010181 |

Dimensions

| | |
|------------|--|
| Dimensions | 3.69 in x 3.38 in x 4.359999999999999 in |
| Height | 4.359999999999999 in |
| Length | 3.69 in |
| Weight | 89 lb |
| Width | 3.38 in |

Electrical Ratings

| | |
|------------------|-----------|
| Frequency Rating | 50/60 Hz |
| Primary Voltage | 208/277 V |

Logistics

| | |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|