Industrial Control Transformer .250KVA 240X480-120 F0

By Acme Electric Catalog ID: TB250N008F0



By Acme Electric

Catalog ID: TB250N008F0

ICT .250KVA 240X480-120 F0

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

Product Details

General

Feedback

Application	Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized without sacrificing secondary voltage stability beyond practical limits.The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type,	
	step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.	
Color	Black	
Secondary Voltage	120 V	
UPC	047503010754	
kVA	.250	
Dimensions		
Dimensions	4.547 in x 4.5 in x 5.2897 in	
Height	5.2897 in	
Length	4.547 in	
Weight	10 lb	
Width	4.5 in	
Length Weight	4.547 in 10 lb	

Electrical Ratings

Frequency Rating	50/60 Hz	
Primary Voltage	240 X 480 V	
Certifications and Compliance		
Certified Listed	UL ListedcUL Listed	
Logistics		Feedback
Carton Quantity	1	Ŭ L
Pallet Quantity	72	