



\* Representative image

## TF279300S

by Acme Electric

Catalog ID: TF279300S

Prop65\_Cancer&amp;Reproductive

Low Voltage Distribution Transformer - Single Phase, 190/200/208/220  
380V/400/416/440 - 110/220V, 1kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

|                      |                                                 |
|----------------------|-------------------------------------------------|
| CE Compliant         | CE Marked                                       |
| Construction         | Encapsulated                                    |
| Electrostatic Shield | Shielded                                        |
| Max Temperature Rise | 115 Degrees Celsius                             |
| Mounting Type        | Wall                                            |
| Primary Voltage      | 190 / 200 / 208 / 220 X 380 / 400 / 416 / 440 V |
| Product Category     | Dry Type Distribution Transformer               |
| Secondary Voltage    | 110/220 V                                       |
| UL Insulation Class  | 180°C                                           |
| UPC                  | 047503841747                                    |
| Winding Material     | CU                                              |
| kVA                  | 1                                               |

### Dimensions

|        |         |
|--------|---------|
| Height | 10.5 in |
| Length | 5.13 in |
| Weight | 24 lb   |
| Width  | 5.5 in  |

### Electrical Ratings

|                  |                                     |
|------------------|-------------------------------------|
| Frequency Rating | 50/60 Hz                            |
| Primary Voltage  | 190/200/208/220 X 380/400/416/440 V |

### Certifications and Compliance

|              |              |
|--------------|--------------|
| CE Compliant | CE Marked    |
| CSA Standard | C22.2 No. 47 |
| Nema Rating  | NEMA 3R      |

|             |        |
|-------------|--------|
| UL Standard | UL 506 |
|-------------|--------|