



# Compression Splice Conventional (Two Die) Full Tension

by FARGO  
Catalog ID: TJA7929

Compression Splice, Conventional 2-Die, Full Tension , for ACSR 4/0 AWG  
6/1



\* Representative image

## Product Details

### General

Aluminum Die	75AH
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	12 to
Tension Range	0 lb
UPC	096359482697

### Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Diameter - Outside	0.563 in
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	15.6 in
Weight	0.980 lb

### Electrical Ratings

Voltage Application	Standard
---------------------	----------

### Conductor Related

Conductor Compatibility	ACSR-Penguin-4/0-6/1
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Type	ACSR
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

### Certifications and Compliance

UL Listed	No
-----------	----

### Logistics

Pallet Quantity	900 EA
-----------------	--------

**For further technical assistance, please contact us**

**Domestic Customer Service**

Hubbell Power Systems

210 N. Allen Centralia, MO 65240 USA

Phone: (573) 682-5521

Fax: (573) 682-8475

Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

**International Customer Service**

Phone: +1-573-682-5521

Fax: +1-573-682-8516

Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)