

## CC384-22TH (R)-SS STANDARD Stainless Steel 15/25kV

By Trinetics  
Catalog # 63488009

Available in sizes for use on single- and three-phase systems rated 200A or 600A.



\*Representative Image

### Features

- Durable powder-paint finish exceeds ANSI C57.12.28 standards,
- Light gray mounting bars for high visibility in adverse weather.
- Munsell green (7GY 3.29/1.5) blends with surroundings.
- Alternative colors are available upon request.

### General

Enclosure Type	Top Hinged Sectionalizing Cabinet
Material	Stainless Steel
Type	Flip Top Sectionalizing
UPC	096359706212

### Dimensions

Dimensions	22.000 in x 84.000 in x 30.000 in
Height	30.000 in
Length	22.000 in
Weight	315 lb
Width	84.000 in

### Electrical Ratings

Current Rating	200 A
Phase	Three Phase

### Product Assets

[Catalogs - Trinetics® Metal Sectionalizing Cabinets and Primary Pedestals \(BR10317E\)](#)  
[Sales Drawings - 63488009](#)