

2 Pole, 100 Amp Relay

By Trinetics  
Catalog # [MR-DNX SPEC 6863](#)

2-pole, 240/480V, Norm Open; Form A air contact, 100A; Load protection: Fuse; Coil voltage: 277V; Control circuit source: Line; Photocell provision: Mounted Receptacle; HOA: Internal ; Control circuit arrester: Spark Gap; in a weather proof case.

Features

The MR Series is the foundation of the Trinetics product line of multiple relay lighting controls. MR relays feature a time-proven electromagnetic design that provides high compression, low audible noise and minimum eddy current heating. For customers in need of heavy duty construction and long-term performance, the MR Series is built for years of trouble-free service in the most challenging environments.

General

Catalog Number	MR-DNX SPEC 6863
Circuit Protection	Fuse
Contact	Air
Contact Configuration	N.O.



Material	Cast Aluminum
Number Of Poles	2
Size	17-1/4 x 11-7/16 x 8-1/4
UPC	096359610595

Electrical Ratings

Amperage Rating	100 A
Coil Voltage	277V
Voltage Rating	240/480 V

Product Assets

[Sales Drawings - Relay Assembly MR-DNX Spec 6863 \(33188400\)](#)  
[Specifications - MRDNXSPEC6863](#)