

TB750N016F2

by Acme Electric

Catalog ID: TB750N016F2



ICT .750KVA 380/400/415 -110X220
F2

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

Product Details

General

Application	Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.
Color	Black
Secondary Voltage	110 X 220 V
UPC	047503012758
kVA	.750

Dimensions

Dimensions	7 in x 5.25 in x 5.91 in
Height	5.91 in
Length	7 in
Weight	28.1 lb
Width	5.25 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	380/400/415 V

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"> • UL Listed • cUL Listed
------------------	---

Logistics

Carton Quantity	1
Pallet Quantity	48