

HUBBELL

Power Systems

1500A 3-phase 600V Secondary Termination Enclosure

By Trinetics
Catalog # TWMMMD-15C20-FTB-N

Trinetics multi-connection secondary termination enclosures provide safe, convenient, and aesthetically pleasing connection points for multiple services suitable for up to 600V. These enclosures are suitable for low voltage splicing or cable termination from the secondary side of a utility's transformer for multiple service feeds. Dual-access enclosure with 2-point locking system and tamperproof louvers, plus copper bus bar punched for NEMA 2-hole spade connectors for continuous current rating through 6000A.



Features

- Continuous current up to 6000A.
- Doors front and back for easy access.
- Combination of welded and bolted construction.
- Copper bus bars of high conductivity and punched for NEMA 2-hole spades connectors for up to 20 services (40 services if front and back of bus are used).
- Domed roof for water run-off and rigidity.
- Two-point locking system with padlock hasp and penta-bolt.
- Captive roof holder for ease of operability.
- Tamperproof louvers designed for maximum ventilation.
- One NEMA 2-hole copper ground pad included in standard offering.
- Non-ferrous hardware.
- Standard construction is 14-gauge steel.

General

Application	Meets ANSI C57.12.28 standard NEMA 3R equivalent Lay-in connectors meets ANSI C119.6 specifications
Catalog Number	TWMMMD-15C20-FTB-N
Color	Munsell Green
Connector Type	Copper Bus punched for NEMA 2-hole spade connectors
Enclosure Style	2 door access with 2 point latch
Number Of Ports	14
UPC	096359600480

Dimensions

Depth	42
Height	0 in
Length	0 in
Width	0 in

Electrical Ratings

Current / Amperage Rating	3000 A
Maximum Current Rating Amps Continuous	3000

Conductor Related

Wire Range	N/A
------------	-----

Product Assets

[Catalogs - Trinetics® Metal Sectionalizing Cabinets and Primary Pedestals](#)
[Sales Drawings - 63257644](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TRIN-TWMMMD15C20FTBN-SPEC-EN | REV 6/2024