

HUBBELL Power Systems

2600A 3-phase 600V Secondary Termination Enclosure

By Trinetics
Catalog # TWMMF-26L28-600-N

Trinetics multi-connection secondary termination enclosures provide safe, convenient, and aesthetically pleasing connection points for multiple services suitable for up to 600V. These enclosures are suitable for low voltage splicing or cable termination from the secondary side of a utility's transformer for multiple service feeds. Convertible 360-plus, patented, 5-point entry access enclosure with 2-point locking system and aluminum lay-in connectors for continuous current rating through 4000A.



Features

- Current rating for aluminum lay-in connectors is based on center feed.
- Current rating for copper bus is based on end-to-end feed.
- Two times the number of cables may be connected if front and back of bus are used.
- Please consult the factory or your local sales representative for any requirements not listed here.

General

Application	Meets ANSI C57.12.28 standard NEMA 3R equivalent Lay-in connectors meets ANSI C119.6 specifications
Catalog Number	TWMMF-26L28-600-N
Color	Munsell Green
Connector Type	Aluminum 2-set screw lay-in Connectors
Enclosure Style	5 point access with 2 point latch
Number Of Ports	18

Dimensions

Depth	36
Height	48 in
Width	36 in

Electrical Ratings

Current / Amperage Rating	4000 A
Maximum Current Rating Amps Continuous	4000

Conductor Related

Wire Range 1/0-750

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TRIN-TWMMF26L28600N-SPEC-EN | REV 6/2024