



* Representative image

Aluminum Compression Terminal for #4 AL/CU, #2 sol CU, #4 6/1, 7/1 ACSR, #2 COMPACT

by ANDERSON
Catalog ID: VAUL412

Aluminum Compression Terminal for #4 AL/CU, #2 sol CU, #4 6/1, 7/1 ACSR, #2 COMPACT, 1 HOLE, Meets ANSI C119.4 Class C performance on copper conductor

- Connectors are prefilled with rubber compatible inhibitor and sealed with color coded end caps.

Product Details

General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Die Index	5/8 (243, BG)
Die Size	*See Resources / Downloads for die selection and installation instructions
Material	Aluminum
Material - Body	Aluminum
Number of Pad Holes	1
Plating	No
Style	Impact Extruded
UPC	096359334903

Dimensions

Diameter - Pad Bolt	0.5 in
Weight	0.098 lb

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18
Conductor Diameter (VersaCrimp) - Maximum	0.268 in
Conductor Diameter (VersaCrimp) - Minimum	0.146 in

Certifications and Compliance

UL Listed	No
-----------	----

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com