



WC924B

by Wiegmann
Catalog ID: WC924B

NI2 Console Body 48X24X18 Carbon Steel - Gray

Designed to house electrical and electronic controls, instruments and components. Heavy duty construction provides protection from dirt, dust, oil and water. Sloping front control panel provides an ideal surface for mounting pushbuttons, pilot lights, meters and switches. Interior components can be mounted on panels located on the sides and back of the enclosure. (Panels are optional).

Product Details

General

Application	Designed to house electrical and electronic controls, instruments, and components. Heavy duty construction provides protection from dirt, dust, oil, and water. Sloping front control panel provides an ideal surface for mounting pushbuttons, pilot lights, m
Color	Gray
Construction	Continuously Welded Seams
Finish Type	Polyester Powder
Latches Type	3-Point Keylocking Handle
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Mounting Collar Studs
Series	WC9
Type	Console Body
UPC	786725441808

Dimensions

Actual Height	48.130 in
Depth	18 in
Height	48 in
Weight	150 lb
Width	24 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 12
UL Listed	Yes