

EdgeConnect™, 5362STR, No ear & threaded hole

By Hubbell Wiring Device-Kellems
Catalog # [5362STRM2](#)

EdgeConnect™, Straight Blade Duplex Receptacle, 20A, No ear & threaded hole, Red

Features

- Back wired screwless termination for faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Simple color coded plungers for easy and quick wiring
- Use small screwdriver to lift plunger and rewire as needed

Application

Spring clamp terminal strengthens over time providing a more reliable connection.

General

Catalog Number	5362STRM2
Color	Red
Flammability	UL 94 V-2
Item Type	Receptacle
Material	Thermoplastic/C
Number Of Poles	2-Pole
Operating Temperature	<ul style="list-style-type: none">• Maximum continuous 75 °C• (w/o impact)minimum -40 °C
Series	EdgeConnect™
Size	3.28x1.58x1.38
Specifications	<ul style="list-style-type: none">• Product Identification- Ratings are a permanent part of the device• Terminal Accommodation- #14 - #10AWG Wire (Solid or Stranded) Copper or UL listed CCA conductors only• Terminal Identification- Terminals Identified in Accordance with UL 498 and CSA



Style	Finder Groove
Type	Short strap, no ears
UPC	783585792460

Electrical Ratings

Current / Amperage Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Industry Standard(s)	UL Listed to UL498 File No. E2186, c-UL-us No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK A-20 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - PD3029](#)
- [Literature - EdgeConnect™ Technology FAQ](#)
- [Literature - EdgeConnect™ Technology](#)
- [Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
- [Sales Drawings - M-14824](#)
- [Specifications - 5362STRM2](#)
- [Warranty - Industrial & Commercial Products](#)