



Straight Blade Devices, Tamper Resistant, Duplex Receptacle, Hubbell-Pro, Hospital Grade, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, White

By Hubbell Wiring Device-Kellems
 Catalog # [8200WTRA](#)



Straight Blade Devices, Tamper Resistant, Duplex Receptacle, Hubbell-Pro, Hospital Grade, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, White

Features

- Tamper-resistant shutter complies with national electrical code requirements
- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

Application

Hubbell-Pro Heavy Duty Hospital Grade

General

Color	<ul style="list-style-type: none"> • White • Blanc
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94V-2 • Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
----------------------	---

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - Wiring M8 Catalog page](#)
- [Catalog Page - Wiring A-22 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs: 4, 6, 8 and 10 inch](#)
- [Literature - Tamper-Resistant Receptacles for Healthcare](#)
- [Literature - WLBD026_Duct Products Brochure_WEB](#)
- [Literature - Healthcare Product Solutions](#)
- [Literature - Healthcare Application Guide](#)
- [Literature - Hubbell-PRO Hospital Grade TR Receptacles](#)
- [Literature - Heavy Duty Tamper-Resistant Receptacles](#)
- [Literature - Tamper-Resistant Receptacles](#)
- [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)

- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Series	Hubbell-Pro
Style	Smooth Face
Type	Receptacle
UPC	783585542225

Dimensions

Dimensions	3.28 in x 1.57 in x 1.15 in
Height	1.15 in
Length	3.28 in
Weight	0.2 lb
Width	1.57 in

through
[Literature - Hubbell-Pro Hospital Grade Receptacles](#)
[Literature - Emergency Preparedness for Healthcare](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Tamper-Resistant Receptacles](#)

Related Products

8200GYTRA - Straight Blade Devices, Tamper Resistant Duplex Receptacle, Hubbell-Pro, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Gray

HBL8215CT - Straight Blade Devices, Male Plug, Insulgrip, Hospital Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Transparent, Single Pack

P8W - Wallplate, 1-Gang, 1) Duplex, White

HBL8215CAT - Straight Blade Devices, Male Plug, Insulgrip, Hospital Grade, Angled, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Transparent, Single Pack

8200BKTRA - Straight Blade Devices, Tamper Resistant Duplex Receptacle, Hubbell-Pro, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Black



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
 WDK-8200WTRA-SPEC-EN | REV 5/2023