

**UltraVac 24kV, 150kV BIL, 200A
Solid Dielectric Vacuum Switch
Compact, 18"**

By Trinetics
Catalog # [33247601C](#)



20kV, 125kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards

Features

- Our most flexible line of switches, UltraVac vacuum capacitor switches can accommodate a wide variety of switching applications while simultaneously offering a unique combination of longevity.
- Such as maintenance-free operation, durability, reliability, high dielectric strength, easy installation and performance that surpasses ANSI standards.
- UltraVac switches are designed for 110kV, 125kV and 150kV BIL applications.
- Best-in-class C2 restrike rating.
- 5-pin auxiliary receptacle included standard, but optional auxiliary contacts are available.

General

Catalog Number	33247601C
Interruption Type	Cycloaliphatic Epoxy
Operating Mechanism	Solenoid
Switch Type	Vacuum in solid dielectric
Type	UltraVac - Compact

Electrical Ratings

Creep and Leakage Distance	18"
Current Rating	200 A
Operating Voltage	120 VAC
Phase	Single Phase

Product Assets

[Specifications - 33247601C](#)