



Wiring Device-Kellems

Vacancy Sensors, Wall Switch, AdaptiveUltrared, 2 Circuit, 120/277V AC, Black

By Hubbell Wiring Device-Kellems
Catalog # [AU2001BK22](#)

Vacancy Sensors, Wall Switch, AdaptiveUltrared, 2 Circuit, 120/277V AC, Black

Features

- Manual ON (Vacancy)
- Built in photocell with manual super saver mode for daylight harvesting
- Designed for use on 120 or 277V AC circuits. No neutral needed for fast retrofits

General

Color	Black
Series	Ultrasonic
Type	Manual
UPC	783585428857

Electrical Ratings

Voltage Rating	120/277 VAC
Voltage Rating Description	120/277V AC

Logistics

Carton Quantity	10
-----------------	----



Product Assets

[Catalog Page - Wiring E-5 Catalog Page](#)
[Catalogs - Wiring Full Catalog](#)
[Installation Manuals - WIRING_PD2768_INSTALLINST](#)
[Warranty - HMOSS Occupancy Motion Sensors](#)

Related Products

[SS26 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) GFCI Opening, Standard Size, Stainless Steel](#)
[AD2000BK22N - Occupancy/Vacancy Sensors, Wall Switch, Adaptive Dual Technology, 2 Circuit, 120/277V AC, No Buttons, Black](#)
[P26BK - Wallplate, 1-Gang, 1\) Decorator, Black](#)
[AD2000BK1N - Wall Switch, Occupancy or Vacancy, Dual Tech, 800W Incandescent, 1000W Fluorescent @ 120V AC, 1800W Fluorescent @ 277V AC, 120/277V AC, With Photocell](#)
[AD2000BK1 - Wall Switch, Occupancy or Vacancy, Dual Tech, 800W Incandescent, 1000W Fluorescent @ 120V AC, 1800W Fluorescent @ 277V AC, 120/277V AC](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-AU2001BK22-SPEC-EN | REV 5/2023