



Vacancy Sensors, Wall Switch, AdaptiveUltrasonic, 2 Circuit, 120/277V AC, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [AU200I122](#)

Vacancy Sensors, Wall Switch, AdaptiveUltrasonic, 2 Circuit, 120/277V AC, Ivory

Features

- Manual ON (Vacancy)
- Built in photocell with manual super saver mode for daylight harvesting
- Designed for use on 120 or 277V AC circuits. No neutral needed for fast retrofits

General

Color	Ivory
Series	Ultrasonic
Type	Manual
UPC	783585428871

Electrical Ratings

Voltage Rating	120/277 VAC
Voltage Rating Description	120/277V AC

Logistics

Carton Quantity	10
-----------------	----



Product Assets

[Catalog Page - Wiring E-5 Catalog Page](#)
[Catalogs - Wiring Full Catalog](#)
[Installation Manuals - WIRING_PD2768_INSTALLINST](#)
[Warranty - HMOSS Occupancy Motion Sensors](#)

Related Products

[AD2000I22 - Occupancy/Vacancy Sensors, Wall Switch, Adaptive Dual Technology, 2 Circuit, 120/277V AC, Ivory](#)
[AD2000I1N - Wall Switch, Occupancy or Vacancy, Dual Tech, 800W Incandescent, 1000W Fluorescent @ 120V AC, 1800W Fluorescent @ 277V AC, 120/277V AC, With Photocell](#)
[P26I - Wallplate, 1-Gang, 1\) Decorator, Ivory](#)
[AD2000I22N - Occupancy/Vacancy Sensors, Wall Switch, Adaptive Dual Technology, 2 Circuit, 120/277V AC, No Buttons, Ivory](#)
[AD2000I1 - Wall Switch, Occupancy or Vacancy, Dual Tech, 800W Incandescent, 1000W Fluorescent @ 120V AC, 1800W Fluorescent @ 277V AC, 120/277V AC](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-AU200I122-SPEC-EN | REV 5/2023