

# HUBBELL Power Systems

## UltraVac 15kV, 125kV BIL, 200A Solid Dielectric Vacuum Switch, 27"

By Trinetics  
Catalog # [33249401](#)

15kV, 125kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) willdlife guards



### Features

- Our most flexible line of switches, UltraVac vacuum capacitor switches can accommodate a wide variety of switching applications while simultaneously offering a unique combination of longevity.
- Such as maintenance-free operation, durability, reliability, high dielectric strength, easy installation and performance that surpasses ANSI standards.
- UltraVac switches are designed for 110kV, 125kV and 150kV BIL applications.
- Best-in-class C2 restrike rating.
- 5-pin auxiliary receptacle included standard, but optional auxiliary contacts are available.

### General

Catalog Number	33249401
Interruption Type	Cycloaliphatic Epoxy
Operating Mechanism	Motor
Switch Type	Vacuum in solid dielectric
Type	UltraVac
UPC	096359626145

### Electrical Ratings

Creep and Leakage Distance	27"
Current Rating	200 A
Operating Voltage	120 VAC
Phase	Single Phase

### Product Assets