

Hubbell-Pro Residential
AUTOGUARD® Self-Test GFCI
Receptacle, 15A, Light Almond

By Hubbell Wiring Device-Kellems
Catalog # [GF15LA](#)

HUBBELLPRO, GFCI, 15A, Light Almond

Features

- Ground fault EOL indicator
- Comprehensive diagnostics
- No power at face if reverse wired
- Automatic self-grounding staple makes installation ease

Application

- Heavy Duty Commercial Grade

Performance

- Electrical - Amperage - 15A/20A, 20A Feed Thru
- Electrical - Max. Interrupting Capacity - 10,000A
- Electrical - Voltage - 120V AC +10% - 15% (102V to 132V)
- Environmental - Maximum Humidity - 0.95
- Environmental - Operating Temperature - -35°C to 66°C or -30°F to 150°F.

General

Catalog Number	GF15LA
Color	Light Almond
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Specifications	<ul style="list-style-type: none">• Codes - Meets all NEC® and CEC requirements• Frequency - 60 Hz• Trip Level - 4 to 6 mA• Trip Time - .025 second nominal
Type	Standard
UPC	883778450563



Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	Meets UL498 For Receptacles
Nema Rating	5-15R

Logistics

Carton Quantity	10
Pallet Quantity	1760

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - GF15LA AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2490_INSTALLINST](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Residential Catalog](#)
[Literature - HUBBELLPRO Ground Fault Receptacles](#)
[Sales Drawings - WDK_GF15LA_DRAWING_PDF](#)
[Specifications - GF15LA](#)
[Warranty - Industrial & Commercial Products](#)