



Terminal, Compression

by ANDERSON
Catalog ID: VACL2012

VERSAtile Aluminum Compression Terminal, 2/0 str AL/CU, 1 H, 1/2"

- Rated at 34.5 KV. UL listed for aluminum or copper conductors. CSA certified.



* Representative image

Product Details

General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Die Size	*See Resources / Downloads for die selection and installation instructions
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	1
Style	Pressed Tubing
UPC	096359334040

Dimensions

Diameter - Pad Bolt	0.5 in
Weight	0.078 lb

Conductor Related

Conductor Compatibility	ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18
Conductor Diameter (VersaCrimp) - Maximum	0.419 in
Conductor Diameter (VersaCrimp) - Minimum	0.232 in

Certifications and Compliance

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	200 EA
-----------------	--------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com