

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 30A 250V AC, 2-Pole 3-Wire Grounding, Terminal Screws, Blue, Watertight

By Hubbell Wiring Device-Kellems  
Catalog # [HBL330P6W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 30A 250V AC, 2-Pole 3-Wire Grounding, Terminal Screws, Blue, Watertight

Features

- Solid one-piece pins for reliable electrical contact
- Gasketed sealing ring provides watertight seal
- Heavy duty external cord grips

Application

- High Ampacity Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 3,000V AC Min
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - HB or Better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperature - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing.
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL330P6W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole



OEM Brand Name  
Series  
Specifications

Hubbell Wiring Device-Kellems  
HBL Heavy Duty

- Contact Carrier - High-Impact Thermoset
- Housing - Zytel® ST801 Nylon
- Locking Ring - Reinforced Thermoplastic Polyester
- Retainer - High-Impact Thermoset
- Terminal Screws - Stainless Steel

Standard Service  
Watertight Plug  
783585403588

Style  
Type  
UPC

Dimensions

Display Size                      Standard Sized

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Single Phase
Voltage Rating	250 VAC
Voltage Rating Description	250 VAC

Conductor Related

Cord Type	All Portable
Number Of Wires	3-Wire
Wire Size	#12 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Standard C22.2 No. 182.1</li><li>• UL Classified to IEC60309-1</li></ul>
----------------------	--

Nema Rating

- UL Listed, File E146032

Non-NEMA

Logistics

Carton Quantity

10

Pallet Quantity

320

Product Assets

Catalog Page - WDK G-6 Catalog Page

Catalog Page - WDK G-24 Catalog Page

Catalog Page - WDK G-10 Catalog Page

Catalog Page - WDK G-22 Catalog Page

Catalog Page - WDK AA-24 Catalog Page

Catalog Page - WDK K-19 Catalog Page

Catalogs - WDK Catalog Full 2024

Engineering Drawing - HBL330P6W AutoCAD Drawing

Installation Manuals - WIRING\_PD1303\_INSTALLINST

Literature - Advantage™ Series Switch-Rated IEC Pin & Sleeve Devices

Literature - IEC Pin & Sleeve Devices

Literature - PULP & PAPER SOLUTIONS

Literature - Pulp & Paper Solutions

Literature - Dual-Certified IEC Pin & Sleeve Devices

Literature - Hubbell Marine Full Line Catalog

Sales Drawings - WDK\_HBL330P\_DRAWING\_PDF

Specifications - Wiring HBL330P6W Specification Sheet

Warranty - Industrial & Commercial Products

Video - Marine Electrical Products

