

Hubbell Wiring Device Kellems, IEC
Pin and Sleeve, Inlet, 32A 125V, 2-
Pole 3-Wire Grounding, 4X/IP69K

By Hubbell Wiring Device-Kellems
Catalog # [HBL332B4W](#)

Hubbell Wiring Device Kellems, IEC Pin and Sleeve, Inlet, 32A
125V, 2-Pole 3-Wire Grounding, 4X/IP69K

Features

- Rugged one-piece housing
- Thermoset polyester contact carrier
- Solid one-piece pins for reliable electrical contact

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1.
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Cord Grip Retention - Per CSA C22.2 No.182.1 /UL1682
- Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL332B4W
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	2-Pole
Series	Advantage Switch-Rated
Specifications	<ul style="list-style-type: none">• Contact Carrier - High-Impact Thermoset• Gaskets - Solid Neoprene• Housing - Zytel® 101 Nylon• Locking Ring - Reinforced Thermoplastic Polyester



Style	• Phase Pins - Brass
Type	IP69k NEMA 4X
UPC	Watertight Mating Inlet 783585365985

Electrical Ratings

Amperage Rating	32 A
Current / Amperage Rating	32 A
Voltage Rating	100-130 VAC
Voltage Rating Description	100-130 VAC

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified File LR280C• UL Classified to IEC 60309-1 IEC 60309-2• UL Listed, File E146032
----------------------	--

Product Assets

[Catalog Page - WDK G-6 Catalog Page](#)
[Catalog Page - WDK G-10 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL332B4W AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1304_INSTALLINST](#)
[Literature - Advantage™ Series Switch-Rated IEC Pin & Sleeve Devices](#)
[Literature - IEC Pin & Sleeve Devices](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_HBL332B4W_DRAWING_PDF](#)
[Specifications - Wiring HBL332B4W Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Advantage Series Switch-Rated Pin & Sleeve](#)