

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Receptacle, 60A 125V AC, 2-Pole 3- Wire Grounding, Watertight

By Hubbell Wiring Device-Kellems  
Catalog # [HBL360R4W](#)

Heavy Duty IEC Pin and Sleeve Industrial Grade Female Receptacle, 60A 125V AC, 2-Pole 3-Wire Grounding, Terminal Screws, Watertight

Features

- Self-closing gasketed cover
- Color coded housings for easy identification
- Super tough insulated non-metallic housing

Application

High Ampacity Watertight Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstand 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL360R4W
Color	Yellow
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole



OEM Brand Name	Hubbell Wiring Device-Kellems
Series	HBL Heavy Duty
Specifications	<ul style="list-style-type: none"><li>• Cover - Reinforced Thermoplastic Polyester</li><li>• Cover Screw - Nickel-plated brass</li><li>• Gaskets - Solid Neoprene</li><li>• Housing - Zytel® 101 Nylon</li><li>• Mounting Flange - Zytel® 101 Nylon</li></ul>
Style	Standard Service
Type	Watertight Receptacle
UPC	783585403854

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	7500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#8 AWG to #2 AWG

Certifications And Compliance

Industry Standard(s)	Listed To Standard UL1682
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK G-11 Catalog Page](#)

[Catalogs - WDK Catalog Full 2024](#)

[Engineering Drawing - HBL360R4W AutoCAD Drawing](#)

[Installation Manuals - WIRING\\_PD1304\\_INSTALLINST](#)

[Literature - PULP & PAPER SOLUTIONS](#)

[Literature - IEC Pin & Sleeve Devices](#)

[Literature - Pulp & Paper Solutions](#)

[Sales Drawings - WDK\\_HBL360R\\_DRAWING\\_PDF](#)

[Specifications - Wiring HBL360R4W Specification Sheet](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
WDK-HBL360R4W-SPEC-EN | REV 4/2025