



WA306010WF

by Wiegmann
Catalog ID: WA306010WF

N12 Double Door Wall-Mount 30X60X10 Carbon Steel - Gray

Intended for use in housing electrical and electronic controls, instruments, components, and associated wiring, these enclosures incorporate double-hinged doors which provide convenient access. Designed for indoor use in protecting components from dust, dirt, oil, and water.

Product Details

General

Application	Intended for use in housing electronic controls, instruments, components and associated wiring. These enclosures incorporate hinged doors which provide convenient access. Designed for indoor use in protecting components from dust, dirt, oil and water.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Textured
Latches Type	Captivated Screws
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Wall Mount
Number of Doors (Fixed)	2
Type	Enclosure
UPC	786725349203

Dimensions

Depth	10 in
Height	30 in
Weight	150 lb
Width	60 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 12
UL Listed	Yes