



Surge Protective Devices, SPIKESHIELD Surface Mount Block, 50KA, 120/240V AC

By Hubbell Wiring Device-Kellems
Catalog # [HBL3W50](#)



Surge Protective Devices, SPIKESHIELD Surface Mount Block,
50KA, 120/240V AC

Features

- Compact design
- NEMA 4X rating and are UL 1449-3rd edition listed

Application

Surface Mount Brick with Leads

General

EU RoHS Indicator	No
Environmental Conditions	Indoor and Outdoor
Indicator(s) Type	Green Status LED per Line
Item Type	Wired-In Surge Arrestors
Material	Steel
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	-40 Degrees F to 149 Degrees F (-40 C to 65 C)
Performance	<ul style="list-style-type: none"> • Electrical - Diagnostics - Green Status LED per line • Electrical - Surge Current per Phase - 50kA • Environmental - Operating Temperature - -40°F to 160°F(-40°C to 70°C) • Mechanical - Terminal Accommodation - #12 AWG Wire Leads
Response Time	5
Series	Wired-In Surge Devices
Type	50kA
UPC	783585120850

Dimensions

Display Size 50kA Peak

Electrical Ratings

Connectivity	Leads
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	<ul style="list-style-type: none"> • Single Phase 120 VAC • Single Phase 240 VAC
Voltage Rating Description	120/240 VAC Single Phase

Certifications and Compliance

Industry Standard(s) UL1449-3rd Edition

Logistics

Carton Quantity 10

Product Assets

- [Catalog Page - Wiring N-7 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Catalogs - Acme Electric Catalog - Section 9 - Power Conditioning Products](#)
- [Engineering Drawing - HBL3W50 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_HBL3W50_INSTALLINST](#)
- [Literature - SpikeShield® Power Quality Surge Protective Devices](#)
- [Literature - Residential Product Guide](#)
- [Literature - Residential Catalog](#)
- [Sales Drawings - WDK_HBL3W50_DRAWING_PDF](#)
- [Warranty - SPD Series: 320kA, 160kA, 100kA, 120kA, 80MkA & 50kA](#)

Related Products

- [HBL11SA40 - Surge Arrestors, 40KA, 600V AC, Three Delta, Type 1](#)
- [HBL3P120C - Surge Protective Devices, Panel, 120KAPeak Capacity, 120/240V AC, 3-Pole 4-Wire Grounding](#)
- [HBL4SA40 - Surge Arrestors, 40KA, 120/208V AC Three Phase Y, Type 1](#)
- [HBL3P320DB - Surge Protective Devices, Panel, 320KAPeak Capacity, 120/240V AC, 3-Pole 4-Wire Grounding, With Disconnect](#)
- [HBLSDSA36 - Surge Protective Devices, SPIKESHIELD Panel Style, 36KA Single Phase](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HBL3W50-SPEC-EN | REV 5/2023