



## WA603624FS

by Wiegmann  
Catalog ID: WA603624FS

N12 Single Door Freestanding 60X36X24 Carbon Steel - Gray

WA-FS SERIES - 12 GAUGE CARBON STEEL NEMA 12 SINGLE DOOR FREESTANDING ENCLOSURE - ENCLOSURE SIZE 60.12 IN X 36.12 IN X 24.12 IN.

## Product Details

### General

Application	Designed to protect electronic controls, components and instruments in typical industrial environments from dust, dirt, oil and dripping water. These enclosures are used in machine tool applications for housing motor starters, drives, contactors, PLC's as well as a wide variety of other electrical and electronic equipment. The addition of 19-inch rack mounting accessories make these enclosures ideal for providing rugged protection for sensitive rack mounted components in harsh industrial environments. The enclosures are found extensively in automotive, pulp and paper, wood products, textile and similar industries.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Textured
Latches Type	3 Point Keylocking-Padlocking Combo
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	1
Type	Enclosure
UPC	786725417292

### Dimensions

Actual Depth	24.12 in
Actual Height	60.120 in
Actual Width	36.12 in

Depth	24 in
Height	60 in
Weight	325 lb
Width	36 in

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	NEMA 12
UL Listed	Yes