

by Wiegmann Catalog ID: WA723024FSDA

N12 Single Door Dual Access Freestanding 72X30X24 Carbon Steel - Gray

Designed to protect electrical, and electronic controls, components, and instruments in typical industrial environments. Enclosure protects enclosure equipment from dust, dirt, oil, and dripping water. These enclosures are used in machine tool applications for housing motor starters, drivers, contactors, PLC's, as well as a wide variety of other electrical and electronic equipment. The addition of 19-inch rack mounting accessories make these enclosures ideal for providing rugged protection for sensitive rack mounted components in harsh industrial environments. The enclosures are found extensively in found in automotive, pulp and paper, wood products, textile, and similar industries. Style includes single door dual access (single door on front and rear).

Product Details

General

Application	Designed to protect electrical and electronic controls, components, and instruments in typical industrial environments. Enclosures protect enclosure equipment from dust, dirt, oil, and dripping water. These enclosures are used in machine tool applications
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Textured
Latches Type	3 Point Keylocking-Padlocking Combo
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	1
Туре	Enclosure
UPC	786725416103

Dimensions

Actual Depth	24.25 in
Actual Height	72.120 in
Actual Width	30.12 in

Height 72 in Weight 385 lb	Depth	24 in
	Height	72 in
	Weight	385 lb
Width 30 in	Width	30 in

Certifications and Compliance

Certified Listed	• UL • CSA
Nema Rating	NEMA 12
UL Listed	Yes