



## WA726024FSDAD

by Wiegmann  
Catalog ID: WA726024FSDAD

N12 Two Door Dual Access Freestanding 72X60X24 Carbon Steel - Gray

Designed to protect electrical, and electronic controls, components, and instruments in typical industrial environments. Enclosure protects enclosure equipment from dust, dirt, oil, and dripping water. These enclosures are used in machine tool applications for housing motor starters, drivers, contactors, PLC's, as well as a wide variety of other electrical and electronic equipment. The addition of 19-inch rack mounting accessories make these enclosures ideal for providing rugged protection for sensitive rack mounted components in harsh industrial environments. The enclosures are found extensively in found in automotive, pulp and paper, wood products, textile, and similar industries. Style includes two door dual access (overlapping doors on front and rear).

### Product Details

#### General

|                         |   |
|-------------------------|---|
| Application             | Designed to protect electrical and electronic controls, components, and instruments in typical industrial environments. Enclosures protect enclosure equipment from dust, dirt, oil, and dripping water. These enclosures are used in machine tool applications |
| Color                   | Gray  |
| Construction            | Continuously Welded Seams   |
| Cover Type              | Door  |
| Finish Type             | Textured  |
| Latches Type            | 3 Point Keylocking-Padlocking Combo   |
| Listings                | UL, CSA   |
| Material                | Carbon Steel  |
| Mounting Type           | Freestanding  |
| Number of Doors (Fixed) | 2   |
| Type                    | Enclosure   |
| UPC                     | 786725452101  |

#### Dimensions

|               |           |
|---------------|-----------|
| Actual Depth  | 24.25 in  |
| Actual Height | 72.120 in |
| Actual Width  | 60.12 in  |

|        |        |
|--------|--------|
| Depth  | 24 in  |
| Height | 72 in  |
| Weight | 615 lb |
| Width  | 60 in  |

#### Certifications and Compliance

|                  |  |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul> |
| Nema Rating      | NEMA 12  |
| UL Listed        | Yes  |